

PRODUCT INFORMATION PACKET

Model No: ORM10206V1

Catalog No: ORM10206V1

OEM Replacement Motor, 1/5 HP, 1 Ph, 60 Hz, 208-230 V, 1075 RPM, 1 Speed, 48 Frame, ENCLOSED



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	1/5 Hp	Output KW	0.15 kW
Frequency	60 Hz	Voltage	208-230 V
Current	1.4 A	Speed	1075 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	48Y	Enclosure	Totally Enclosed
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications


Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	Extended Studs	Motor Orientation	Any
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Flat
Overall Length	8.49 in	Frame Length	3.25 in
Shaft Diameter	0.500 in	Shaft Extension	4.3 in
Connection Drawing	614131-322	Outline Drawing	ORM10206V1-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2022



A

GROUND LEAD: NO. 18 GA., .03 [8] THK., (GREEN) INSUL.

PERFORMANCE CURVE NO.	TORQUE @1075 RPM (25°C)	APPROVED SAMPLE	UL COMPONENT		CSA	
			FILE #	CCN #	FILE #	CLASS #
C32397	17.8 OZ. FT.	0444592B	E46412	PRGY2	LR43341	4211-01



LEAD DATA		
DRAWING REVISION D	REVISION BY J. RUPESTI	DATE 03-11-2021
DATE 03-11-2021	APPROVED BY J. RUPESTI	DATE 03-11-2021
TCD DESCRIPTION STATION		

DRAWING NO. TW DATE 04-30-2012 APPROVED BY [Signature] DATE 04-30-2012 PRODUCED BY J. HENSH	 Regal Beloit America, Inc. DESCRIPTION MODEL-RFHP-48FR OUTLINE MATERIAL -	THIRD ANGLE PROJECTION 	SIZE / DWG NO. C / ORM102026V1	SHEET 1 OF 1
--	---	--	-----------------------------------	-----------------