

PRODUCT INFORMATION PACKET

Model No: 6703

Catalog No: 6703

Fan and Blower Motor, 1/3 HP, 1 Ph, 60 Hz, 208-230/277 V, 1075 RPM, 5 Speed, 48 Frame, OAO



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	1/3 Hp	Output KW	0.25 kW
Frequency	60 Hz	Voltage	208-230/277 V
Current	2.8/2.6 A	Speed	1075 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	48	Enclosure	Open Air Over
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	5

Technical Specifications

Electrical Type	Electronically Commutated Motor	Poles	12
Rotation	Reversible	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	9.17 in
Frame Length	4.32 in	Shaft Diameter	0.500 in
Shaft Extension	3.92 in		
Connection Drawing	N/R	Outline Drawing	5SME39DXL227

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2022

