

# PRODUCT INFORMATION PACKET

Model No: 9210L

Catalog No: 9210L

1/15-1/20-1/25 HP Refrigeration Motor, 1550 RPM, 1 Speed, 115 Volts, 3.3" Mount, TEAO



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

### Nameplate Specifications

Output HP	1/15 Hp	Output KW	0.05 kW
Frequency	60 Hz	Voltage	115 V
Current	1.25 A	Speed	1550 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	A
Frame	UNIT BEARING	Enclosure	Totally Enclosed Air Over
Thermal Protection	Electronic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

### Technical Specifications

Electrical Type	Electronically Commutated Motor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Lead End
Mounting	Extended Studs	Drive End Bearing	Unit
Opp Drive End Bearing	Unit	Frame Material	Cast Iron
Shaft Type	Flat	Frame Length	3.20 in
Shaft Diameter	0.312 in	Shaft Extension	1.94 in
Outline Drawing	9210L-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/08/2022

