

**Nameplate Specifications**

Phase	1	Output HP	3.0 Hp
Output KW	2.2 kW	Voltage	230 V
Speed	1740 r/min	Service Factor	1
Frame	Y184T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	83 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	13.7 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	206
Opp Drive End Bearing	204	Frame Length	8.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025