

PRODUCT INFORMATION PACKET



Model No: K236
Catalog No: K236
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	1	Output HP	7-10.5 Hp
Output KW	5.2 kW	Voltage	200-230 V
Speed	3480 r/min	Service Factor	1
Frame	Y184TZ	Enclosure	Totally Enclosed Non Ventilated
Efficiency	83.5 %	Ambient Temperature	50 °C
Frequency	60 Hz	Current	45-40 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	206sff
Opp Drive End Bearing	206sff	Frame Length	10.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025