

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 75 Hp | Output KW | 55.0 kW |
| Frequency | 60 Hz | Voltage | 380 V |
| Current | 114.9 A | Speed | 892 rpm |
| Service Factor | 1.25 | Phase | 3 |
| Efficiency | 93.6 % | Power Factor | 0.78 |
| Duty | S1 | Insulation Class | F |
| Frame | 280S/M | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6317 | Opp Drive End Bearing Size | 6317 |
| UL | No | CSA | No |
| CE | No | IP Code | 55 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 8 | Rotation | Clockwise |
| Mounting | B3 | Motor Orientation | Horizontal |
| Drive End Bearing | C3 | Opp Drive End Bearing | C3 |
| Frame Material | Cast | Shaft Type | Keyed |
| Overall Length | 1111 mm | Frame Length | 600 mm |
| Shaft Diameter | 75 mm | Shaft Extension | 140 mm |
| Assembly/Box Mounting | TOP | | |
| Outline Drawing | 0228000589 | | |