

Nameplate Specifications

Output HP	3 Hp	Output KW	2.2 kW
Voltage	180 V	Current	14.0 A
Speed	1750 rpm	Service Factor	1
Efficiency	88.8 %	Duty	Continuous
Insulation Class	H	Frame	182/145TC
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	6205
Opp Drive End Bearing Size	6204	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	19.60 in	Shaft Diameter	0.875 in
Shaft Extension	2.15 in	Torque	108 LB-IN
Outline Drawing	033315	Connection Drawing	00531901

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2022