



Nameplate Specifications

Output HP	3 Hp	Output KW	2.2 kW
Voltage	180 V	Speed	1750 rpm
Service Factor	1.0	Frame	112MD
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Efficiency	88.8 %	Ambient Temperature	40 °C
Current	14.0 A	Duty	S1
Insulation Class	H	Drive End Bearing Size	6205
Opp Drive End Bearing Size	6204	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	B3/B14
Overall Length	19.75 in	Shaft Diameter	0.937 in
Shaft Extension	2.04 in	Torque	108 LB-IN
Outline Drawing	034374		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/03/2023