

### Nameplate Specifications

Output HP	0 Hp	Frequency	- Hz
Voltage	- V	Current	- A
Phase	3	Duty	Continuous
Insulation Class	F	Design Code	NO DESIGN CODE
KVA Code	-	Frame	184T
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Ambient Temperature	0 °C	Drive End Bearing Size	6206
Opp Drive End Bearing Size	6205	UL	No
CSA	N	CE	N
IP Code	43	Number of Speeds	1

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	T
Assembly/Box Mounting	F1 ONLY		
Connection Drawing	NONE	Outline Drawing	035757-900

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022