



### Nameplate Specifications

Output HP	4 Hp	Output KW	3.0 kW
Frequency	60 Hz	Voltage	480 V
Current	5.8 A	Speed	1740 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	H
Design Code	B	KVA Code	L
Frame	182TZ	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermostat	Ambient Temperature	70 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	3.84 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Special Extension Both Sides	Assembly/Box Mounting	F3
Connection Drawing	005102.09	Outline Drawing	OL131937

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/30/2023