

PRODUCT INFORMATION PACKET

Model No: 132353.00

Catalog No: 132353.00

..7HP..none.184.TENV.34V.3PH.none.special.40C.1.0SF.....

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	7 Hp	Output KW	5.2 kW
Frequency	NONE Hz	Voltage	34 V
Current	NONE A	Service Factor	1
Phase	3	Duty	ELECTRIC VEHICLE
Insulation Class	F	Design Code	NO DESIGN CODE
KVA Code	NONE	Frame	184
Enclosure	Totally Enclosed Non Ventilated	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	NONE
Opp Drive End Bearing Size	NONE	UL	No
CSA	N	CE	N
IP Code	43	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.0075 Ohms	Mounting	PARTIAL MOTOR
Motor Orientation	Horizontal	Frame Material	Rolled Steel
Assembly/Box Mounting	F1/F2 CAPABLE		
Connection Drawing	NONE	Outline Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022