

Nameplate Specifications

Output HP	7 Hp	Output KW	5.2 kW
Frequency	NONE Hz	Voltage	34 V
Current	NONE A	Service Factor	1
Phase	3	Duty	ELECTRIC VEHICLE
Insulation Class	F	Design Code	NO DESIGN CODE
KVA Code	NONE	Frame	184TZ
Enclosure	Totally Enclosed Non Ventilated	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	NONE
Opp Drive End Bearing Size	NONE	UL	No
CSA	N	CE	N
IP Code	43	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	.0075 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1 ONLY		
Outline Drawing	NONE	Connection Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022