



Nameplate Specifications

Phase	3	Output HP	SPECIAL Hp
Voltage	- V	Speed	1111 rpm
Frame	184TZ	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	No Protection	Ambient Temperature	40 °C
Frequency	- Hz	Current	- A
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	E
Drive End Bearing Size	NONE	Opp Drive End Bearing Size	NONE
UL	No	CSA	N
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Rotation	Reversible	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1 ONLY
Outline Drawing	OL132404	Connection Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024