

PRODUCT INFORMATION PACKET

Model No: 132408.00

Catalog No: 132408.00

ROTOR SHAFT ASSEMBLY.....184TZ.TENV..3PH..CONT.40C..PARTIAL MOTOR.....

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	0 Hp	Frequency	60 Hz
Voltage	- V	Current	No Voltage A
Service Factor	1	Duty	Continuous
Insulation Class	F	Design Code	NO DESIGN CODE
KVA Code	-	Frame	184TZ
Enclosure	Totally Enclosed Non Ventilated	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	NONE
Opp Drive End Bearing Size	NONE	UL	No
CSA	N	CE	N
IP Code	43	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Rotation	Reversible	Mounting	PARTIAL MOTOR
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Connection Drawing	NONE	Outline Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022