

**Nameplate Specifications**

Phase	1	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	230 V
Speed	1730 r/min	Service Factor	1
Frame	F215T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	86.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	39.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	307
Opp Drive End Bearing	206	Frame Length	9.00 in
Connection Drawing	33575301.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025