

PRODUCT INFORMATION PACKET



Model No: K327
Catalog No: K327
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	1	Output HP	10.0-12.0 Hp
Output KW	7.5 kW	Voltage	230 V
Speed	1720 r/min	Service Factor	1
Frame	D215TZ	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	40-48 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	307sff
Opp Drive End Bearing	307sff	Frame Length	10.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025