



Nameplate Specifications

Phase	3	Voltage	575 V
Speed	1745 rpm	Efficiency	85.5 %
Current	1.1 A	Duty	Continuous
KVA Code	L	UL	Recognized
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Poles	4
Resistance Main	0 Ohms	Motor Orientation	Horizontal
Drive End Bearing	Ball	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	VARIABLE 10:1		
Outline Drawing	0214300002	Connection Drawing	EE7300

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/18/2024