

PRODUCT INFORMATION PACKET



Model No: E2013
Catalog No: E2013
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	3.0 Hp
Output KW	2.2 kW	Voltage	230/460 V
Speed	1765 r/min	Service Factor	1.15
Frame	S182T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	87.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	8.2/4.1 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Counterclockwise
Drive End Bearing	206szz	Opp Drive End Bearing	206szz
Frame Length	8.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025