



**Nameplate Specifications**

Phase	<b>3</b>	Output HP	<b>5.0 Hp</b>
Output KW	<b>3.7 kW</b>	Voltage	<b>230/460 V</b>
Speed	<b>1745 r/min</b>	Service Factor	<b>1.15</b>
Frame	<b>S184TC</b>	Enclosure	<b>Totally Enclosed Fan Cooled</b>
Thermal Protection	<b>No Protection</b>	Ambient Temperature	<b>40 °C</b>
Frequency	<b>60 Hz</b>	Current	<b>13.0/6.5 A</b>
Duty	<b>Continuous</b>	Insulation Class	<b>F</b>
UL	<b>Recognized</b>	CSA	<b>Y</b>
Number of Speeds	<b>1</b>		

**Technical Specifications**

Rotation	<b>Reversible</b>	Mounting	<b>Rigid Base</b>
Drive End Bearing	<b>Ball</b>	Opp Drive End Bearing	<b>Ball</b>

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025