

# PRODUCT INFORMATION PACKET



Model No: E207  
Catalog No: E207  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

|            |            |                     |            |
|------------|------------|---------------------|------------|
| Phase      | 3          | Output HP           | 2.0 Hp     |
| Output KW  | 1.5 kW     | Voltage             | 230/460 V  |
| Speed      | 1180 r/min | Service Factor      | 1.15       |
| Frame      | E184T      | Enclosure           | Drip Proof |
| Efficiency | 87 %       | Ambient Temperature | 40 °C      |
| Frequency  | 60 Hz      | Current             | 7.4/3.7 A  |
| Duty       | Continuous | Insulation Class    | F          |
| CSA        | Y          |                     |            |

**Technical Specifications**

|                       |              |                   |            |
|-----------------------|--------------|-------------------|------------|
| Poles                 | 6            | Rotation          | Reversible |
| Mounting              | Rigid Base   | Drive End Bearing | 206        |
| Opp Drive End Bearing | 204          | Frame Length      | 9.25 in    |
| Connection Drawing    | 80022802.PCX |                   |            |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025