

**Nameplate Specifications**

|            |            |                     |                                 |
|------------|------------|---------------------|---------------------------------|
| Phase      | 3          | Output HP           | 5.0 Hp                          |
| Output KW  | 3.7 kW     | Voltage             | 230/460 V                       |
| Speed      | 1740 r/min | Service Factor      | 1.15                            |
| Frame      | F184TC     | Enclosure           | Totally Enclosed Non Ventilated |
| Efficiency | 87.5 %     | Ambient Temperature | 40 °C                           |
| Frequency  | 60 Hz      | Current             | 12.4/6.2 A                      |
| Duty       | Continuous | Insulation Class    | B                               |
| UL         | Recognized | CSA                 | N                               |

**Technical Specifications**

|                       |            |                   |            |
|-----------------------|------------|-------------------|------------|
| Poles                 | 4          | Rotation          | Reversible |
| Mounting              | Rigid Base | Drive End Bearing | 206        |
| Opp Drive End Bearing | 204        | Frame Length      | 7.25 in    |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025