

**Nameplate Specifications**

Phase	3	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	230/460 V
Speed	1745 r/min	Service Factor	1.15
Frame	S184JM	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	15/7.5 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball Brg
Frame Length	7.75 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025