



Nameplate Specifications

Phase	3	Output HP	5.0 (3.7KW) Hp
Voltage	230/460 V	Speed	1745 r/min
Service Factor	1.25	Frame	S184JM
Enclosure	Drip Proof	Ambient Temperature	40 °C
Frequency	60 Hz	Current	15/7.5 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Round	Drive End Bearing	Ball Brg
Frame Length	7.75 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025