

**Nameplate Specifications**

Phase	3	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	230/460 V
Speed	1740 r/min	Service Factor	1.15
Frame	S184JM	Efficiency	82.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	13.6/6.8 A	Duty	Continuous
Insulation Class	B		

Technical Specifications

Rotation	Reversible	Drive End Bearing	207
Opp Drive End Bearing	206		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025