

**Nameplate Specifications**

Phase	3	Output HP	7.5 Hp
Output KW	5.6 kW	Voltage	230/460 V
Speed	3450 r/min	Service Factor	1.15
Frame	S184JM	Efficiency	85.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	17.6/8.8 A	Duty	Continuous
Insulation Class	B		

Technical Specifications

Rotation	Reversible	Drive End Bearing	207
Opp Drive End Bearing	204		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025