

# PRODUCT INFORMATION PACKET



Model No: E3006  
Catalog No: E3006  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	230/460 V
Speed	1740 r/min	Service Factor	1.15
Frame	S215TC	Enclosure	Drip Proof
Efficiency	89.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	25.8/12.9 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Counterclockwise
Drive End Bearing	208sf	Opp Drive End Bearing	206sf
Frame Length	11.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025