

PRODUCT INFORMATION PACKET



Model No: E3013
Catalog No: E3013
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	230/460 V
Speed	1745 r/min	Service Factor	1.15
Frame	S215T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	89.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	25.6/12.8 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible Counterclockwise
Drive End Bearing	208szz	Opp Drive End Bearing	206szz
Frame Length	11.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025