

PRODUCT INFORMATION PACKET



Model No: E3028
Catalog No: E3028
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	230/460 V
Speed	3490 r/min	Service Factor	1.15
Frame	184TC	Efficiency	87.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	12/6 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	206
Opp Drive End Bearing	206		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025