

# PRODUCT INFORMATION PACKET



Model No: E3036  
Catalog No: E3036  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	50.0 Hp
Output KW	37.3 kW	Voltage	230/460 V
Speed	3540 r/min	Service Factor	1.15
Frame	326TSC	Efficiency	92.4 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	109/54.5 A	Duty	Continuous
Insulation Class	F		

**Technical Specifications**

Rotation	Reversible	Drive End Bearing	313
Opp Drive End Bearing	311		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025