

# PRODUCT INFORMATION PACKET



Model No: E368  
Catalog No: E368  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	7.5 (5.6KW) Hp
Voltage	200-230/460 V	Speed	1760 r/min
Service Factor	1.15	Frame	S213JM
Enclosure	Drip Proof	Efficiency	87.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	22-21/10.5 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

**Technical Specifications**

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	310
Opp Drive End Bearing	206	Frame Length	9.60 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025