

PRODUCT INFORMATION PACKET



Model No: E371M
Catalog No: E371M
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	230/460 V
Speed	3520 r/min	Service Factor	1.15
Frame	D213JM	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	27/13.5 A	Duty	Continuous
Insulation Class	F	CSA	Y

Technical Specifications

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball Brg
Frame Length	10.60 in		
Connection Drawing	80022802		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025