

**Nameplate Specifications**

Phase	3	Output HP	150 Hp
Output KW	111.9 kW	Voltage	460 V
Speed	1790 r/min	Service Factor	1.15
Frame	445T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	95 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	172 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	6318
Opp Drive End Bearing	6318	Frame Length	0.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025