



Nameplate Specifications

| | | | |
|------------|-------------------|---------------------|--|
| Phase | 3 | Output HP | 150 Hp |
| Output KW | 111.9 kW | Voltage | 460 V |
| Speed | 1790 r/min | Service Factor | 1.15 |
| Frame | 445T | Enclosure | Totally Enclosed Non Ventilated |
| Efficiency | 95.8 % | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 172 A |
| Duty | Continuous | Insulation Class | F |
| UL | Recognized | CSA | Y |

Technical Specifications

| | | | |
|-----------------------|-------------------|-------------------|-------------------|
| Poles | 4 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | 6318 |
| Opp Drive End Bearing | 318 | Frame Length | 0.00 in |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025