

**Nameplate Specifications**

Phase	3	Output HP	250 Hp
Output KW	186.5 kW	Voltage	460 V
Speed	1190 r/min	Service Factor	1.15
Frame	449T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	95.8 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	299 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	6	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	6319
Opp Drive End Bearing	6318	Frame Length	0.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025