

# PRODUCT INFORMATION PACKET



Model No: E4124  
Catalog No: E4124  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





**Nameplate Specifications**

|            |                   |                     |                   |
|------------|-------------------|---------------------|-------------------|
| Phase      | <b>3</b>          | Output HP           | <b>150.0 Hp</b>   |
| Output KW  | <b>111.9 kW</b>   | Voltage             | <b>460 V</b>      |
| Speed      | <b>1785 r/min</b> | Service Factor      | <b>1.15</b>       |
| Frame      | <b>444T</b>       | Enclosure           | <b>Drip Proof</b> |
| Efficiency | <b>95 %</b>       | Ambient Temperature | <b>40 °C</b>      |
| Frequency  | <b>60 Hz</b>      | Current             | <b>164 A</b>      |
| Duty       | <b>Continuous</b> | Insulation Class    | <b>F</b>          |
| UL         | <b>Recognized</b> | CSA                 | <b>Y</b>          |

**Technical Specifications**

|                       |                   |                   |                                    |
|-----------------------|-------------------|-------------------|------------------------------------|
| Poles                 | <b>4</b>          | Rotation          | <b>Reversible Counterclockwise</b> |
| Mounting              | <b>Rigid Base</b> | Drive End Bearing | <b>6318</b>                        |
| Opp Drive End Bearing | <b>6318</b>       | Frame Length      | <b>0.00 in</b>                     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025