

PRODUCT INFORMATION PACKET



Model No: E4134
Catalog No: E4134
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

| | | | |
|------------|------------|---------------------|------------|
| Phase | 3 | Output HP | 400 Hp |
| Output KW | 298.4 kW | Voltage | 460 V |
| Speed | 1785 r/min | Service Factor | 1.15 |
| Frame | 449T | Enclosure | Drip Proof |
| Efficiency | 95.8 % | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 437 A |
| Duty | Continuous | Insulation Class | F |
| CSA | Y | | |

Technical Specifications

| | | | |
|-----------------------|------------|-------------------|-----------------------------|
| Poles | 4 | Rotation | Reversible Counterclockwise |
| Mounting | Rigid Base | Drive End Bearing | 6319 |
| Opp Drive End Bearing | 6318 | Frame Length | 19.20 in |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025