

**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	230/460 V
Speed	1170 r/min	Service Factor	1.15
Frame	S256T	Enclosure	Drip Proof
Efficiency	90.2 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	28.4/14.2 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	6	Rotation	Counterclockwise
Drive End Bearing	309sf	Opp Drive End Bearing	207sf
Frame Length	13.00 in		
Connection Drawing	80022801.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025