

**Nameplate Specifications**

|                    |               |                     |                             |
|--------------------|---------------|---------------------|-----------------------------|
| Phase              | 3             | Output HP           | 30.0 Hp                     |
| Output KW          | 22.4 kW       | Voltage             | 575 V                       |
| Speed              | 1775 r/min    | Service Factor      | 1.15                        |
| Frame              | 286T          | Enclosure           | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C                       |
| Frequency          | 60 Hz         | Current             | 29.1 A                      |
| Duty               | Continuous    | Insulation Class    | F                           |
| UL                 | Recognized    | CSA                 | Y                           |
| Number of Speeds   | 1             |                     |                             |

**Technical Specifications**

|                   |            |                       |            |
|-------------------|------------|-----------------------|------------|
| Rotation          | Reversible | Mounting              | Rigid Base |
| Drive End Bearing | Ball       | Opp Drive End Bearing | Ball       |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025