

**Nameplate Specifications**

Phase	3	Output HP	25.0 18.7KW Hp
Output KW	1361.5 kW	Voltage	200-230/460 V
Speed	1765 r/min	Service Factor	1.15
Frame	S284JM	Enclosure	Drip Proof
Efficiency	91 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	67-60/30 A
Duty	Continuous	Insulation Class	F
CSA	Y		

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	313
Opp Drive End Bearing	210	Frame Length	15.08 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025