



### Nameplate Specifications

Phase	3	Output HP	100 Hp
Output KW	74.6 kW	Voltage	460 V
Speed	3565 r/min	Service Factor	1.15
Frame	365TS	Efficiency	93.6 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	110 A	Duty	Continuous
Insulation Class	F		

### Technical Specifications

Rotation	Reversible	Drive End Bearing	6312
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025