



Nameplate Specifications

| | | | |
|---------------------|------------|----------------|------------|
| Phase | 3 | Output HP | 50 Hp |
| Output KW | 37.3 kW | Voltage | 230/460 V |
| Speed | 1190 r/min | Service Factor | 1.15 |
| Frame | 365T | Efficiency | 94.1 % |
| Ambient Temperature | 40 °C | Frequency | 60 Hz |
| Current | 119/59.5 A | Duty | Continuous |
| Insulation Class | F | | |

Technical Specifications

| | | | |
|-----------------------|-----------------------------|-------------------|------|
| Rotation | Reversible Counterclockwise | Drive End Bearing | 6314 |
| Opp Drive End Bearing | 6312 | | |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025