

PRODUCT INFORMATION PACKET



Model No: E735
Catalog No: E735
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

| | | | |
|---------------------|------------|----------------|------------|
| Phase | 3 | Output HP | 75.0 Hp |
| Output KW | 56.0 kW | Voltage | 200 V |
| Speed | 1785 r/min | Service Factor | 1.15 |
| Frame | Y365T | Efficiency | 95 % |
| Ambient Temperature | 40 °C | Frequency | 60 Hz |
| Current | 200 A | Duty | Continuous |
| Insulation Class | F | | |

Technical Specifications

| | | | |
|-----------------------|------------|-------------------|-----|
| Rotation | Reversible | Drive End Bearing | 314 |
| Opp Drive End Bearing | 212 | | |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025