

**Nameplate Specifications**

Phase	3	Output HP	60 Hp
Output KW	44.8 kW	Voltage	230/460 V
Speed	1785 r/min	Service Factor	1.15
Frame	364TS	Efficiency	95 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	140/70 A	Duty	Continuous
Insulation Class	F		

**Technical Specifications**

Rotation	Reversible Counterclockwise	Drive End Bearing	6314
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025