

PRODUCT INFORMATION PACKET



Model No: E930V1
Catalog No: E930V1
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	30.0 Hp
Output KW	22.4 kW	Voltage	575 V
Speed	1770 r/min	Service Factor	1.15
Frame	S286T	Enclosure	Drip Proof
Efficiency	94.1 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	28.5 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Counterclockwise
Drive End Bearing	311sf	Opp Drive End Bearing	207sf
Frame Length	15.50 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025