

# PRODUCT INFORMATION PACKET



Model No: E932  
Catalog No: E932  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	50 Hp
Output KW	37.3 kW	Voltage	575 V
Speed	1780 r/min	Service Factor	1.15
Frame	326T	Efficiency	94.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	47 A	Duty	Continuous
Insulation Class	F		

**Technical Specifications**

Rotation	Reversible Counterclockwise	Drive End Bearing	6312
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025