

# PRODUCT INFORMATION PACKET



Model No: K203  
Catalog No: K203  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

|            |            |                     |                                 |
|------------|------------|---------------------|---------------------------------|
| Phase      | 1          | Output HP           | 3.0 Hp                          |
| Output KW  | 2.2 kW     | Voltage             | 115/230 V                       |
| Speed      | 1750 r/min | Service Factor      | 1                               |
| Frame      | S184T      | Enclosure           | Totally Enclosed Non Ventilated |
| Efficiency | 78.5 %     | Ambient Temperature | 40 °C                           |
| Frequency  | 60 Hz      | Current             | 32.0/16.0 A                     |
| Duty       | Continuous | Insulation Class    | F                               |
| UL         | Recognized | CSA                 | Y                               |

**Technical Specifications**

|                       |            |                   |            |
|-----------------------|------------|-------------------|------------|
| Poles                 | 4          | Rotation          | Reversible |
| Mounting              | Rigid Base | Drive End Bearing | 206        |
| Opp Drive End Bearing | 204        | Frame Length      | 7.75 in    |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025