

**Nameplate Specifications**

Phase	1	Output HP	7.5-10.5 Hp
Output KW	5.6 kW	Voltage	200-230 V
Speed	3450 r/min	Service Factor	1
Frame	S215TZ	Enclosure	Drip Proof
Efficiency	84.4 %	Ambient Temperature	50 °C
Frequency	60 Hz	Current	43-38 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	307sff
Opp Drive End Bearing	307sff	Frame Length	9.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025