



### Nameplate Specifications

Phase	3	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	575 V
Speed	1750 r/min	Service Factor	1.15
Frame	184T	Efficiency	89.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	5.2 A	Duty	Continuous
Insulation Class	F		

### Technical Specifications

Rotation	Reversible	Drive End Bearing	206
Opp Drive End Bearing	206		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025