

**Nameplate Specifications**

|                     |               |            |              |
|---------------------|---------------|------------|--------------|
| Phase               | 3             | Output HP  | 5.0 3.7KW Hp |
| Voltage             | 200-230/460 V | Speed      | 1745 r/min   |
| Service Factor      | 1.15          | Frame      | S184TCZ      |
| Enclosure           | Drip Proof    | Efficiency | 85.5 %       |
| Ambient Temperature | 40 °C         | Frequency  | 60 Hz        |
| Current             | 15.5-15/7.5 A | Duty       | Continuous   |
| Insulation Class    | F             | CSA        | Y            |

**Technical Specifications**

|                       |            |                   |            |
|-----------------------|------------|-------------------|------------|
| Poles                 | 4          | Rotation          | Reversible |
| Mounting              | Rigid Base | Drive End Bearing | 207        |
| Opp Drive End Bearing | 204        | Frame Length      | 7.75 in    |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025