

**Nameplate Specifications**

Phase	3	Output HP	7.5 Hp
Output KW	5.6 kW	Voltage	230/460 V
Speed	3450 r/min	Service Factor	1.15
Frame	S184TCZ	Efficiency	85.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	17.6/8.8 A	Duty	Continuous
Insulation Class	B		

**Technical Specifications**

Rotation	Reversible	Drive End Bearing	207
Opp Drive End Bearing	204		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025